OUTSERTS

LARGE QUANTITIES OF TEXTS IN A COMPACT SPACE.





The boxes do not get bigger, but the amount of text needed on the leaflet is rising steadily.



To achieve the smallest possible material thickness, we are using specially developed papers as from 40g/m^2 . Internal developments with reduced grammage such as 32 and 37g/m^2 are already in progress.

In addition to the folding materials with such a low grammage, also printing, cutting and counting is a high challenge.

The outserts can be closed earthier with adhesives or with labels systems.

- Maximum thickness: 10mm
- Number of panels: 110 (upgradeable to 170 panels)

Before folding, a camera system checks whether the correct print sheet is present and whether it's been printed on both sides.

To provide a compact, wrinkle, and tear-free fold, water scoring comes into use. With a very fine waterjet, suppling the crease line before its folded.

Outserts are usually delivered in trays.

If even more text in a small space is required, Multi-inserts or Mini-booklets are further product specialties from RATTPACK. Supplying already suitable solutions to the pharmaceutical sector.



Outserts

